


KOMET® base body, 6×D, Ø DC: 46mm

Order data

| | |
|--------------|---------------|
| Order number | 236652 46 |
| GTIN | 4047109095946 |
| Item class | 24K |

Description
Version:

- **Process reliable up to 6×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

| | |
|--|-----------------|
| ABS® shank Ø D _s | 80 mm |
| suitable for drilling head | 46 - 54 mm |
| Base body Ø d ₁ | 44.5 mm |
| Overall length L _{tot} | 375 mm |
| Reach L ₁ | 310 mm |
| Nominal Ø D | 46 |
| Drill depth for indexable insert drill up to | 6×D |
| Shank | ABS |
| Through-coolant | yes |
| Type of product | Indexable drill |

