

**KOMET KUB Centron® Powerline drill head, Ø DC: 27mm****Order data**

Order number	236651 27
GTIN	4047109227002
Item class	24L

**Description****Version:**

The drill point guides the tool precisely on the axis of the hole, thus ensuring both straightness and very high process reliability, with stability in hole depths up to 9×D.

Spot drilling on flat level surfaces without a pilot hole.

Drill head without slide bars and slide bar adjustment.

**Application:**

For rotating and stationary as well as vertical and horizontal use in all materials.

With centring tip No. 236659.

With indexable inserts No. 236520 – 236576.

**Note:**

Further sizes available on request.

**Technical description**

Pack of insert screws	239652 8IP1 (1.3 Nm)
Screw for base body	239653 8IP9
ISO code indexable insert	SOEX 07T308
Number of cutting edges Z	2
Base body size	26
Centring tip size	40

Series	KUB Centron®
Nominal Ø D	27
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	Drilling blind holes
Through-coolant	yes
Type of product	Indexable drill

---

## Accessories

Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torx Plus® insert screw set10 pieces Drive 8IP1	239652 8IP1
Torx Plus® insert screw set10 pieces Drive 8IP9	239653 8IP9