

**Garant**
**Clamping toolholder, right-hand, Shank / insert size: 25/16mm**

**Order data**

Order number	251008 25/16
GTIN	4045197650672
Item class	21T

**Technical description**

Shim pins pack	259044 3
Head length L <sub>1</sub>	32 mm
Insert size	16 mm
Shank size	25 mm
suitable indexable insert	KNUX 1604.. R/L
Functional width L <sub>4</sub>	32 mm
Screw for clamp	259021 3
Shim	259031 4
Clamp	259038 16
Spring	259046 3
ISO code toolholder	CKJNR/L 2525M16
Overall length L	150 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Set of shim pins 10 pieces Type 3	259044 3
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Spring Type 3	259046 3
Shim Type 4	259031 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Screw for clamping claw Type 3	259021 3
Clamping claw Type 16	259038 16
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600