


KOMET KUB Centron® Powerline drill head, Ø DC: 37mm

Order data

Order number	236651 37
GTIN	4047109227101
Item class	24L

Description
Version:

The drill point guides the tool precisely on the axis of the hole, thus ensuring both straightness and very high process reliability, with stability in hole depths up to 9×D.

Spot drilling on flat level surfaces without a pilot hole.

Drill head without slide bars and slide bar adjustment.

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

With centring tip No. 236659.

With indexable inserts No. 236520 – 236576.

Note:

Further sizes available on request.

Technical description

Screw for base body	239653 15IP
Centring tip size	50
Pack of insert screws	239652 20IP (6.3 Nm)
Base body size	33
ISO code indexable insert	SOEX 120508
Number of cutting edges Z	2

Series	KUB Centron®
Nominal Ø D	37
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	Drilling blind holes
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torx Plus® insert screw set 10 pieces Drive 20IP	239652 20IP
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Torx Plus® insert screw set 10 pieces Drive 15IP	239653 15IP
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600