


KOMET® base body, 6×D, Ø DC: 65mm

Order data

Order number	236652 65
GTIN	4047109095960
Item class	24K

Description
Version:

- **Process reliable up to 6×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

Overall length L_{tot}	500 mm
Reach L_1	420 mm
ABS® shank $\varnothing D_s$	80 mm
Base body $\varnothing d_1$	63.5 mm
suitable for drilling head	65 - 71 mm
Nominal $\varnothing D$	65
Drill depth for indexable insert drill up to	6×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

