


**KOMET® base body, 8×D, Ø DC: 20mm**

**Order data**

Order number	236654 20
GTIN	4047109076211
Item class	24K

**Description**
**Version:**

- **Process reliable up to 8 (9)×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

**Application:**

For rotating and stationary as well as vertical and horizontal use in all materials.

**Note:**

Further sizes and spare parts on request.

**Technical description**

Overall length $L_{tot}$	235 mm
ABS® shank $\varnothing D_s$	50 mm
Reach $L_1$	200 mm
Base body $\varnothing d_1$	19 mm
suitable for drilling head	20 - 25 mm
Nominal $\varnothing D$	20
Drill depth for indexable insert drill up to	8×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

