

Garant
Clamping toolholder, right-hand, Shank / insert size: 32/08mm

Order data

Order number	251912 32/08
GTIN	4045197656957
Item class	21T

Technical description

Shank size	32 mm
Functional width L ₄	40 mm
Pin	259049 2
Shim	259031 41
ISO code toolholder	MWLNRL 3232P08
Clamping claw	259038 12
Insert size	8 mm
suitable indexable insert	WN.. 0804..
Head length L ₁	32 mm
Screw set	259023 2
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw Type 12	259038 12
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Shim Type 41	259031 41
Pin Type 2	259049 2
Set of screws 10 pieces Type 2	259023 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500