

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 25/08mm

Order data

| | |
|--------------|---------------|
| Order number | 251936 25/08 |
| GTIN | 4045197651419 |
| Item class | 21T |

Technical description

| | |
|--|----------------|
| Pin | 259049 3 |
| Shim | 259031 41 |
| Clamping claw | 259038 12 |
| Minimum pre-drill $\varnothing D_{\min}$ | 32 mm |
| Centre offset L_3 | 17 mm |
| suitable indexable insert | WN.. 0804.. |
| Insert size | 8 mm |
| ISO code toolholder | A25R MWLNR/L08 |
| Screw set | 259023 3 |
| Overall length L | 200 mm |
| Clamping height L_2 | 24 mm |
| Setting angle κ | 95 degrees |
| Shank $\varnothing D_s$ | 25 mm |
| Standard | DIN 8024 |
| Application type | right-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |

| | |
|-----------------|-------------------------------|
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Pin Type 3 | 259049 3 |
| Clamping claw Type 12 | 259038 12 |
| Shim Type 41 | 259031 41 |
| Set of screws 10 pieces Type 3 | 259023 3 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |