


KOMET KUB Centron® Powerline drill head, Ø DC: 29mm

Order data

Order number	236651 29
GTIN	4047109227026
Item class	24L

Description
Version:

The drill point guides the tool precisely on the axis of the hole, thus ensuring both straightness and very high process reliability, with stability in hole depths up to 9×D.

Spot drilling on flat level surfaces without a pilot hole.

Drill head without slide bars and slide bar adjustment.

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

With centring tip No. 236659.

With indexable inserts No. 236520 – 236576.

Note:

Further sizes available on request.

Technical description

Number of cutting edges Z	2
ISO code indexable insert	SOEX 07T308
Centring tip size	60
Base body size	26
Pack of insert screws	239652 8IP1 (1.3 Nm)
Screw for base body	239653 8IP9

Series	KUB Centron®
Nominal Ø D	29
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	Drilling blind holes
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torx Plus® insert screw set10 pieces Drive 8IP9	239653 8IP9
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torx Plus® insert screw set10 pieces Drive 8IP1	239652 8IP1