


KOMET® base body, 6×D, Ø DC: 72mm

Order data

Order number	236652 72
GTIN	4047109095977
Item class	24K

Description
Version:

- **Process reliable up to 6×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

suitable for drilling head	72 - 81 mm
Reach L_1	460 mm
Base body $\varnothing d_1$	70.5 mm
ABS® shank $\varnothing D_s$	100 mm
Overall length L_{tot}	540 mm
Nominal $\varnothing D$	72
Drill depth for indexable insert drill up to	6×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

