

**KNUX 160405L, Grade: HB7010****Order data**

Order number	251072 HB7010
GTIN	4045197663931
Item class	21G

Description

KNUX 160405L HB7010 Chip breaker: SG
Chip diverter: 3.2 mm
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 110 - 280 m/min

Technical description

ISO code indexable insert	KNUX 160405L
Insert assignment	left-hand
Type of product	