

Garant
Clamping toolholder, left-hand, Shank / insert size: 20/16mm

Order data

Order number	251009 20/16
GTIN	4045197654649
Item class	21T

Technical description

Functional width L ₄	30 mm
ISO code toolholder	CKJNR/L 2020K16
Insert size	16 mm
Screw for clamp	259021 3
Spring	259046 3
Shank size	20 mm
suitable indexable insert	KNUX 1604.. R/L
Shim pins pack	259044 3
Shim	259031 6
Clamp	259038 17
Head length L ₁	32 mm
Overall length L	125 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Clamping claw Type 17	259038 17
Screw for clamping claw Type 3	259021 3
Shim Type 6	259031 6
Set of shim pins 10 pieces Type 3	259044 3
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Spring Type 3	259046 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600