

Clamping toolholder, left-hand, Shank / insert size: 20/16mm



Order data

| | |
|--------------|---------------|
| Order number | 251009 20/16 |
| GTIN | 4045197654649 |
| Item class | 21T |

Technical description

| | |
|---------------------------|-------------------------------|
| Functional width L_4 | 30 mm |
| ISO code toolholder | CKJNR/L 2020K16 |
| Insert size | 16 mm |
| Screw for clamp | 259021 3 |
| Spring | 259046 3 |
| Shank size | 20 mm |
| suitable indexable insert | KNUX 1604.. R/L |
| Shim pins pack | 259044 3 |
| Shim | 259031 6 |
| Clamp | 259038 17 |
| Head length L_1 | 32 mm |
| Overall length L | 125 mm |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 93 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm | 659906 1600 |
| 8 mm blade with magnetwith 1/4 inch bit holder overall length 50 mm | 659874 50 |
| Clamping claw Type 17 | 259038 17 |
| Screw for clamping claw Type 3 | 259021 3 |
| Shim Type 6 | 259031 6 |
| Set of shim pins10 pieces Type 3 | 259044 3 |
| PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm | 674242 4 |
| Spring Type 3 | 259046 3 |
| Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm | 659957 1600 |