

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 32/08mm


Order data

Order number	251936 32/08
GTIN	4045197651426
Item class	21T

Technical description

Pin	259049 5
ISO code toolholder	A32S MWLNR/L08
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Centre offset L_3	22 mm
Clamping claw	259038 12
suitable indexable insert	WN.. 0804..
Insert size	8 mm
Shim	259031 41
Screw set	259023 3
Overall length L	250 mm
Clamping height L_2	31 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	32 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamping claw Type 12	259038 12
Pin Type 5	259049 5
Shim Type 41	259031 41
Set of screws 10 pieces Type 3	259023 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500