


KOMET KUB Centron® Powerline drill head, Ø DC: 30mm

Order data

Order number	236651 30
GTIN	4047109227033
Item class	24L

Description
Version:

The drill point guides the tool precisely on the axis of the hole, thus ensuring both straightness and very high process reliability, with stability in hole depths up to 9×D.

Spot drilling on flat level surfaces without a pilot hole.

Drill head without slide bars and slide bar adjustment.

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

With centring tip No. 236659.

With indexable inserts No. 236520 – 236576.

Note:

Further sizes available on request.

Technical description

Base body size	26
Pack of insert screws	239652 15IP1 (2.8 Nm)
Screw for base body	239653 8IP9
Number of cutting edges Z	2
ISO code indexable insert	SOEX 090408
Centring tip size	40

Series	KUB Centron®
Nominal Ø D	30
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	Drilling blind holes
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torx Plus® insert screw set10 pieces Drive 8IP9	239653 8IP9
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torx Plus® insert screw set10 pieces Drive 15IP	239652 15IP