


KOMET® base body, 8×D, Ø DC: 33mm

Order data

Order number	236654 33
GTIN	4047109076273
Item class	24K

Description
Version:

- **Process reliable up to 8 (9)×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

Reach L_1	290 mm
suitable for drilling head	33 - 39.2 mm
Overall length L_{tot}	330 mm
Base body $\varnothing d_1$	32 mm
ABS® shank $\varnothing D_s$	50 mm
Nominal $\varnothing D$	33
Drill depth for indexable insert drill up to	8×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

