

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 20/06mm****Order data**

Order number	251917 20/06
GTIN	4045197651365
Item class	21T

**Technical description**

ISO code toolholder	PWLNLR/L 2020K06
Insert size	6 mm
Lever screw	259018 6
Lever	259015 9
Shim punches pack	259047 3
Functional width L <sub>4</sub>	25 mm
suitable indexable insert	WN.. 0604..
Shank size	20 mm
Head length L <sub>1</sub>	16 mm
Shim	259031 25
Shim pins pack	259044 5
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Shim Type 25	259031 25
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5
Lever screw Type 6	259018 6
Shim punches set10 pieces Type 3	259047 3
Set of shim pins10 pieces Type 5	259044 5
Lever Type 9	259015 9
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500