


**KOMET® base body, 4×D, Ø DC: 26mm**

**Order data**

Order number	236653 26
GTIN	4047109076228
Item class	24K

**Description**
**Version:**

- **Process reliable up to 4×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

**Application:**

For rotating and stationary as well as vertical and horizontal use in all materials.

**Note:**

Further sizes and spare parts on request.

**Technical description**

Reach $L_1$	130 mm
suitable for drilling head	26 - 32 mm
Base body $\varnothing d_1$	25 mm
ABS® shank $\varnothing D_s$	50 mm
Overall length $L_{tot}$	160 mm
Nominal $\varnothing D$	26
Drill depth for indexable insert drill up to	4×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

