


KOMET® base body, 8×D, Ø DC: 40mm

Order data

Order number	236654 40
GTIN	4047109076181
Item class	24K

Description
Version:

- **Process reliable up to 8 (9)×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

Overall length L_{tot}	390 mm
ABS® shank $\varnothing D_s$	63 mm
Base body $\varnothing d_1$	38.5 mm
suitable for drilling head	40 - 45 mm
Reach L_1	340 mm
Nominal $\varnothing D$	40
Drill depth for indexable insert drill up to	8×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

