


KOMET KUB Centron® Powerline drill head, Ø DC: 21mm

Order data

Order number	236651 21
GTIN	4047109226944
Item class	24L

Description
Version:

The drill point guides the tool precisely on the axis of the hole, thus ensuring both straightness and very high process reliability, with stability in hole depths up to 9×D.

Spot drilling on flat level surfaces without a pilot hole.

Drill head without slide bars and slide bar adjustment.

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

With centring tip No. 236659.

With indexable inserts No. 236520 – 236576.

Note:

Further sizes available on request.

Technical description

Pack of insert screws	239652 6IP2 (1.0 Nm)
Screw for base body	239653 8IP8
Base body size	20
Centring tip size	10
ISO code indexable insert	SOEX 060306
Number of cutting edges Z	2

Series	KUB Centron®
Nominal Ø D	21
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	Drilling blind holes
Through-coolant	yes
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 6IP	674252 6IP
Torx Plus® insert screw set 10 pieces Drive 8IP8	239653 8IP8
Torque screwdriver, fixed setting set torque 1,0 N·m	211750 1,0
Torx Plus® insert screw set 10 pieces Drive 6IP2	239652 6IP2