


KOMET® base body, 8×D, Ø DC: 46mm

Order data

Order number	236654 46
GTIN	4047109095984
Item class	24K

Description
Version:

- **Process reliable up to 8 (9)×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

suitable for drilling head	46 - 54 mm
Base body Ø d ₁	44.5 mm
Overall length L _{tot}	480 mm
ABS® shank Ø D _s	80 mm
Reach L ₁	415 mm
Nominal Ø D	46
Drill depth for indexable insert drill up to	8×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

