

HEDI

Cable reel for F, B, PL, CZ, Type: 15N



Order data

Order number	081195 15N
GTIN	4003644017003
Item class	08B

Description

Version:

Cable reel with **guided automatic draw-in and roll-up, with multiple stop points per revolution**. High-impact enclosed **plastic housing**. Thermal **overload cut-out**, sturdy H07RN-F neoprene cable with connection point.

Easy to mount on the wall or ceiling with **150° pivoting range**.

Function:

IP24: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided.

Application:

Improved ergonomics by relieving cable tension, and for ensuring tidiness and avoiding the risk of accidents and injuries due to cables lying on the ground.

Note:

For spring return hose reels see No. 080066 to 080079.

Technical description

Material cable	Neoprene rubber
Width	185 mm
Cable structure	3G1.5
Length	325 mm

Rated power unrolled	2000 (16 A) W
Cable length	15 m
Type	15N
Height	275 mm
Cable class	H07RN-F
Body material	Plastic
Nominal voltage	250 V
IP Index of Protection	IP 24
Power supply	Mains operated
Plug type, input	E
Type of product	Cable reel