


**KOMET® base body, 4×D, Ø DC: 33mm**

**Order data**

Order number	236653 33
GTIN	4047109076259
Item class	24K

**Description**
**Version:**

- **Process reliable up to 4×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

**Application:**

For rotating and stationary as well as vertical and horizontal use in all materials.

**Note:**

Further sizes and spare parts on request.

**Technical description**

Base body Ø d <sub>1</sub>	32 mm
ABS® shank Ø D <sub>s</sub>	50 mm
Overall length L <sub>tot</sub>	195 mm
Reach L <sub>1</sub>	160 mm
suitable for drilling head	33 - 39.2 mm
Nominal Ø D	33
Drill depth for indexable insert drill up to	4×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

