


KOMET® base body, 6×D, Ø DC: 20mm

Order data

Order number	236652 20
GTIN	4047109076204
Item class	24K

Description
Version:

- **Process reliable up to 6×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

Overall length L_{tot}	185 mm
suitable for drilling head	20 - 25 mm
Base body $\varnothing d_1$	19 mm
ABS® shank $\varnothing D_s$	50 mm
Reach L_1	150 mm
Nominal $\varnothing D$	20
Drill depth for indexable insert drill up to	6×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

