


KOMET® base body, 6×D, Ø DC: 26mm

Order data

Order number	236652 26
GTIN	4047109076235
Item class	24K

Description
Version:

- **Process reliable up to 6×D.**
- **Stiff joint between base body and drill head.**
- **Shank type ABS.**

Application:

For rotating and stationary as well as vertical and horizontal use in all materials.

Note:

Further sizes and spare parts on request.

Technical description

ABS® shank Ø D _s	50 mm
Reach L ₁	175 mm
suitable for drilling head	26 - 32 mm
Overall length L _{tot}	210 mm
Base body Ø d ₁	25 mm
Nominal Ø D	26
Drill depth for indexable insert drill up to	6×D
Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

