

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 32/08mm

Order data

Order number	251942 32/08
GTIN	4045197656988
Item class	21T

Technical description

Shim	259031 40
Shim punches pack	259047 2
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Lever	259015 2
suitable indexable insert	WN.. 0804..
Insert size	8 mm
Shim pins pack	259044 2
Centre offset L_3	22 mm
Lever screw	259018 2
ISO code toolholder	A32S PWLNR/L08
Overall length L	250 mm
Clamping height L_2	31 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	32 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 40	259031 40
Lever screw Type 2	259018 2
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Lever Type 2	259015 2
Shim punches set10 pieces Type 2	259047 2
Set of shim pins10 pieces Type 2	259044 2
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500