

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 40/08mm

Order data

Order number	251937 40/08
GTIN	4045197651464
Item class	21T

Technical description

Centre offset L_3	27 mm
Pin	259049 5
Screw set	259023 3
Clamping claw	259038 12
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Insert size	8 mm
suitable indexable insert	WN.. 0804..
ISO code toolholder	A40T MWLNR/L08
Shim	259031 41
Overall length L	300 mm
Clamping height L_2	38.5 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Pin Type 5	259049 5
Set of screws 10 pieces Type 3	259023 3
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamping claw Type 12	259038 12
Shim Type 41	259031 41
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500