

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 16/06mm


Order data

Order number	251943 16/06
GTIN	4045197651495
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	21 mm
ISO code toolholder	A16M PWLNR/L06
Centre offset L_3	11 mm
suitable indexable insert	WN.. 0604..
Lever	259015 14
Insert size	6 mm
Lever screw	259018 10
Overall length L	150 mm
Clamping height L_2	15.25 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2
Lever Type 14	259015 14
Lever screw Type 10	259018 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
