

**Garant**
**Lever lock toolholder, right-hand, Shank / insert size: 25/06mm**

**Order data**

Order number	251916 25/06
GTIN	4045197651310
Item class	21T

**Technical description**

Lever	259015 9
Lever screw	259018 6
Functional width L <sub>4</sub>	32 mm
suitable indexable insert	WN.. 0604..
Shim	259031 25
ISO code toolholder	PWLNRL 2525M06
Shim pins pack	259044 5
Shank size	25 mm
Head length L <sub>1</sub>	16 mm
Shim punches pack	259047 3
Insert size	6 mm
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Lever screw Type 6	259018 6
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5
Set of shim pins 10 pieces Type 5	259044 5
Shim Type 25	259031 25
Shim punches set 10 pieces Type 3	259047 3
Lever Type 9	259015 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500