

# HEDI

## Machine lamp, Type: 9LED



### Order data

Order number	081300 9LED
GTIN	4003644017027
Item class	08B

### Description

#### Version:

High-quality, universally usable lamps, with on/off switch, 3-m rubber connection cable. Robust, long, coated flexible metal arm for good mobility of the lamp head and high stability.

All Hedi® machine/workstation lamps come with table clamps, integrated magnet and 4 screws for flexible attachment of the lamp to a wide variety of surfaces as standard.

Proven machine lamp with extremely sturdy lamp head, protected against splashed water and dust-tight, for professional use in tough working environments or use on and in machines. Radio interference suppression according to DIN EN 62493. Machine lamp with **LEDs** for directed illumination of the workplace. Low power consumption, avoids heating up the illuminated objects and subjecting them to UV radiation.

Lamp head with improved joint.

#### Function:

IP20: No protection against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and no protection against water.

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Bulb, with **strong magnetic clamp, 50 mm screw-on clamp, and mounting screws** for machine, table, wall or ceiling attachment.

IP Index of Protection: IP 64

Nominal voltage: 250 V  
Light focussing: focussed tight beam  
Beam dispersion angle fixed: 60 °  
Light output: 9 W  
Illumination: 1000 lm

## Technical description

Illumination	1000 lm
Bulb	LED
Power supply	Mains-powered
IP Index of Protection	IP 64
Lamp replaceable	no
Light output	9 W
Nominal voltage	250 V
Beam dispersion angle fixed	60 °
Light focussing	focussed tight beam
Type of product	Machine lamp