

Garant**Lever lock toolholder, right-hand, Shank / insert size: 32/15mm****Order data**

Order number	251110 32/15
GTIN	4045197656735
Item class	21T

Technical description

Shim punches pack	259047 4
Functional width L ₄	40 mm
Shim pins pack	259044 6
Head length L ₁	30 mm
Shank size	32 mm
ISO code toolholder	PSKNR/L 3232P15
Insert size	15 mm
suitable indexable insert	SN.. 1506..
Shim	259031 37
Lever screw	259018 11
Lever	259015 12
Overall length L	170 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever screw Type 11	259018 11
Shim punches set 10 pieces Type 4	259047 4
Lever Type 12	259015 12
Shim Type 37	259031 37
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of shim pins 10 pieces Type 6	259044 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500