

Garant
Lever lock toolholder, right-hand, Shank / insert size: 32/15mm

Order data

Order number	251112 32/15
GTIN	4045197656780
Item class	21T

Technical description

ISO code toolholder	PSSNR/L 3232P15
Shim punches pack	259047 4
Insert size	15 mm
Shim	259031 37
Lever screw	259018 11
Shim pins pack	259044 6
Head length L ₁	36 mm
Lever	259015 12
suitable indexable insert	SN.. 1506..
Shank size	32 mm
Functional width L ₄	40 mm
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Shim Type 37	259031 37
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Lever screw Type 11	259018 11
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500