

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 25/08mm

Order data

| | |
|--------------|---------------|
| Order number | 251943 25/08 |
| GTIN | 4045197656995 |
| Item class | 21T |

Technical description

| | |
|--------------------------------------|----------------|
| Shim pins pack | 259044 2 |
| Centre offset L ₃ | 17 mm |
| suitable indexable insert | WN.. 0804.. |
| Minimum pre-drill Ø D _{min} | 32 mm |
| Lever screw | 259018 8 |
| Insert size | 8 mm |
| Shim punches pack | 259047 2 |
| Shim | 259031 40 |
| ISO code toolholder | A25R PWLNR/L08 |
| Lever | 259015 2 |
| Overall length L | 200 mm |
| Clamping height L ₂ | 24 mm |
| Setting angle κ | 95 degrees |
| Shank Ø D _s | 25 mm |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 3×D |

| | |
|-----------------|-------------------------------|
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Set of shim pins 10 pieces Type 2 | 259044 2 |
| Shim Type 40 | 259031 40 |
| Shim punches set 10 pieces Type 2 | 259047 2 |
| Lever screw Type 8 | 259018 8 |
| Lever Type 2 | 259015 2 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |