

Garant**Lever lock toolholder, right-hand, Shank / insert size: 32/19mm****Order data**

Order number	251110 32/19
GTIN	4045197650825
Item class	21T

Technical description

Shim pins pack	259044 7
Lever screw	259018 13
suitable indexable insert	SN.. 1906..
Head length L ₁	34 mm
Shim	259031 38
ISO code toolholder	PSKNR/L 3232P19
Shim punches pack	259047 5
Lever	259015 13
Insert size	19 mm
Shank size	32 mm
Functional width L ₄	40 mm
Overall length L	170 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever screw Type 13	259018 13
Lever Type 13	259015 13
Set of shim pins 10 pieces Type 7	259044 7
Shim Type 38	259031 38
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500