

Garant
Screw-on toolholder, left-hand, Shank / insert size: 08/07mm


Order data

Order number	260309 08/07
GTIN	
Item class	21T

Description

Technical description

Insert size	7 mm
Functional width L ₄	10 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	SDJCR/L 0808D07
Shank size	8 mm
Pack of insert screws	269028 22
Head length L ₁	13 mm
Overall length L	60 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Set of insert screws Type 22	269028 22