

Garant
Lever lock toolholder, left-hand, Shank / insert size: 20/12mm

Order data

Order number	251113 20/12
GTIN	4045197650870
Item class	21T

Technical description

Shim punches pack	259047 2
ISO code toolholder	PSSNR/L 2020K12
Shank size	20 mm
Insert size	12 mm
Shim pins pack	259044 2
suitable indexable insert	SN.. 1204..
Head length L ₁	29 mm
Lever	259015 2
Shim	259031 20
Lever screw	259018 2
Functional width L ₄	25 mm
Overall length L	125 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins 10 pieces Type 2	259044 2
Lever screw Type 2	259018 2
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Lever Type 2	259015 2
Shim punches set 10 pieces Type 2	259047 2
Shim Type 20	259031 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500