

Garant
Screw-on toolholder, left-hand, Shank / insert size: 10/07mm

Order data

Order number	260309 10/07
GTIN	4045197655349
Item class	21T

Technical description

ISO code toolholder	SDJCR/L 1010E07
Pack of insert screws	269028 22
Functional width L ₄	12 mm
suitable indexable insert	DC.. 0702..
Head length L ₁	13 mm
Shank size	10 mm
Insert size	7 mm
Overall length L	70 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500