

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 25/12mm****Order data**

Order number	251111 25/12
GTIN	4045197656759
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	32 mm
ISO code toolholder	PSKNR/L 2525M12
Shim	259031 20
suitable indexable insert	SN.. 1204..
Shim punches pack	259047 2
Insert size	12 mm
Shank size	25 mm
Head length L <sub>1</sub>	26 mm
Shim pins pack	259044 2
Lever	259015 2
Lever screw	259018 2
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

### Accessories

Shim punches set 10 pieces Type 2	259047 2
Lever screw Type 2	259018 2
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Set of shim pins 10 pieces Type 2	259044 2
Lever Type 2	259015 2
Shim Type 20	259031 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500