

**Garant****Screw-on toolholder, left-hand, Shank / insert size: 12/07mm****Order data**

Order number	260309 12/07
GTIN	4045197652614
Item class	21T

**Technical description**

Shank size	12 mm
Insert size	7 mm
Pack of insert screws	269028 22
Functional width L <sub>4</sub>	16 mm
suitable indexable insert	DC.. 0702..
Head length L <sub>1</sub>	17 mm
ISO code toolholder	SDJCR/L 1212F07
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500