

Garant
Lever lock toolholder, left-hand, Shank / insert size: 25/15mm

Order data

Order number	251113 25/15
GTIN	4045197656797
Item class	21T

Technical description

Head length L ₁	35 mm
Lever	259015 12
Shank size	25 mm
Insert size	15 mm
ISO code toolholder	PSSNR/L 2525M15
Shim pins pack	259044 6
suitable indexable insert	SN.. 1506..
Shim punches pack	259047 4
Shim	259031 37
Functional width L ₄	32 mm
Lever screw	259018 11
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim punches set 10 pieces Type 4	259047 4
Lever screw Type 11	259018 11
Lever Type 12	259015 12
Set of shim pins 10 pieces Type 6	259044 6
Shim Type 37	259031 37
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500