

Garant
Lever lock toolholder, left-hand, Shank / insert size: 25/15mm

Order data

Order number	251111 25/15
GTIN	4045197656766
Item class	21T

Technical description

Shim	259031 37
Lever	259015 12
Shim pins pack	259044 6
Shim punches pack	259047 4
Head length L ₁	30 mm
ISO code toolholder	PSKNR/L 2525M15
Shank size	25 mm
suitable indexable insert	SN.. 1506..
Functional width L ₄	32 mm
Insert size	15 mm
Lever screw	259018 11
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 37	259031 37
Set of shim pins 10 pieces Type 6	259044 6
Lever Type 12	259015 12
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim punches set 10 pieces Type 4	259047 4
Lever screw Type 11	259018 11
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500