


**SNMG 120408, Grade: CA510**

**Order data**

Order number	251164 CA510
GTIN	4960664698738
Item class	25E

**Description**

SNMG 120408 CA510 Corner radius: 0.8 mm  
 Grade: CA510  
 Chip breaker: PQ  
 Cutting depth  $a_p$ : 0.2 - 2.5 mm  
 Feed  $f$ : 0.13 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 180 - 590 m/min

**Technical description**

Main application	P
Chip breaker	PQ
Cutting conditions	continuous
Feed $f$	0.13 - 0.4 mm/rev.
Corner radius	0.8 mm
Cutting depth $a_p$	0.2 - 2.5 mm
Grade	CA510

Cutting speed $v_c$ main application	180 - 590 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning