

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 32/15mm****Order data**

Order number	251113 32/15
GTIN	4045197656902
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	40 mm
ISO code toolholder	PSSNR/L 3232P15
Shank size	32 mm
Shim	259031 37
Insert size	15 mm
Head length L <sub>1</sub>	36 mm
Lever	259015 12
suitable indexable insert	SN.. 1506..
Lever screw	259018 11
Shim punches pack	259047 4
Shim pins pack	259044 6
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Shim punches set 10 pieces Type 4	259047 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 37	259031 37
Lever screw Type 11	259018 11
Set of shim pins 10 pieces Type 6	259044 6
Lever Type 12	259015 12
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500