

**Garant**
**Lever lock toolholder, left-hand, Shank / insert size: 32/15mm**

**Order data**

Order number	251111 32/15
GTIN	4045197650832
Item class	21T

**Technical description**

Insert size	15 mm
Head length L <sub>1</sub>	30 mm
Lever screw	259018 11
suitable indexable insert	SN.. 1506..
Shim	259031 37
Shim punches pack	259047 4
Lever	259015 12
Functional width L <sub>4</sub>	40 mm
ISO code toolholder	PSKNR/L 3232P15
Shank size	32 mm
Shim pins pack	259044 6
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Lever Type 12	259015 12
Shim Type 37	259031 37
Lever screw Type 11	259018 11
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500