

Garant
Screw-on toolholder, right-hand, Shank / insert size: 08/07mm

Order data

Order number	260308 08/07
GTIN	4045197655318
Item class	21T

Description

Screw-on toolholder 08/07 mm ISO code toolholder: SDJCR/L 0808D07
 suitable indexable insert: DC.. 0702..
 Functional width L_4 : 10 mm
 Head length L_1 : 13 mm
 Overall length L: 60 mm
 Pack of insert screws: 269028 22

Technical description

Insert size	7 mm
Shank size	8 mm
suitable indexable insert	DC.. 0702..
Functional width L_4	10 mm
ISO code toolholder	SDJCR/L 0808D07
Pack of insert screws	269028 22
Head length L_1	13 mm
Overall length L	60 mm
Series	QuickTurn
Application type	right-hand
Standard	DIN ISO 5610

Through-coolant	no
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws 10 pieces	269440
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 22	269028 22