


SNMG 120404, Grade: CA510

Order data

Order number	251162 CA510
GTIN	4960664698721
Item class	25E

Description

SNMG 120404 CA510 Corner radius: 0.4 mm
 Grade: CA510
 Chip breaker: PQ
 Cutting depth a_p : 0.2 - 2.5 mm
 Feed f : 0.13 - 0.4 mm/rev.
 Cutting speed v_c main application: 180 - 590 m/min

Technical description

Corner radius	0.4 mm
Cutting depth a_p	0.2 - 2.5 mm
Cutting conditions	continuous
Main application	P
Chip breaker	PQ
Feed f	0.13 - 0.4 mm/rev.
Grade	CA510

Cutting speed v_c main application	180 - 590 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SNMG 120404
Number of changes/inserts	8
Type of product	Indexable insert for turning