

Garant**Screw-on toolholder, right-hand, Shank / insert size: 10/07mm****Order data**

Order number	260308 10/07
GTIN	4045197655325
Item class	21T

Technical description

ISO code toolholder	SDJCR/L 1010E07
Head length L ₁	13 mm
suitable indexable insert	DC.. 0702..
Functional width L ₄	12 mm
Pack of insert screws	269028 22
Shank size	10 mm
Insert size	7 mm
Overall length L	70 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500