

Garant**Lever lock toolholder, right-hand, Shank / insert size: 20/12mm****Order data**

Order number	251110 20/12
GTIN	4045197656711
Item class	21T

Technical description

Shim punches pack	259047 2
suitable indexable insert	SN.. 1204..
ISO code toolholder	PSKNR/L 2020K12
Insert size	12 mm
Shim pins pack	259044 2
Head length L ₁	26 mm
Functional width L ₄	25 mm
Lever	259015 2
Shim	259031 20
Lever screw	259018 2
Shank size	20 mm
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Data sheet

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 20	259031 20
Lever screw Type 2	259018 2
Lever Type 2	259015 2
Set of shim pins 10 pieces Type 2	259044 2
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Shim punches set 10 pieces Type 2	259047 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500