


KOMET KUB® V464 drill head, Ø DC: 105mm

Order data

Order number	236660 105
GTIN	4047109085565
Item class	24L

Description
Version:

Indexable drill holder (drill head) with indexable insert cartridges and BS® T connection, right-hand cutting. The indexable insert cartridge for the outer indexable insert is adjustable by +5mm on the Ø. Use with arbors in ABS® N and extensions ABS® T. Reliability up to 6×D.

Process reliability up to 6×D.
Application:

With centring point No. 236661 - 236662.
With indexable inserts No. 236740 - 237080.

Supplied with:

Drill head with cartridges.

Note:

Spare parts on request.

Technical description

ABS® T Ø d	63 mm
External Ø d ₁	102.5 mm
Centring tip size	80
ISO code indexable insert	WOEX080404

Pack of insert screws	239655 15IP (6.3 Nm)
Number of cutting edges Z	1
Nominal \varnothing D	105
Overhang L_A	85 mm
Shank	ABS
Use for drilling	Drilling blind holes
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Type of product	Indexable drill

Accessories

KOMET KUB® V464 centring point, HSS Type 80	236662 80
Torx Plus® insert screw set 10 pieces Drive 15IP	239655 15IP
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
KOMET KUB® V464 centring point, HSS Type 80	236661 80
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600