

Garant
Boring bar set carbide, left-hand

Order data

Order number	260325
GTIN	4045197652775
Item class	29W

Description

Boring bar set carbide ISO code toolholder: E10K SDUCR/L07
 ISO code toolholder: E12M SDUCR/L07
 suitable indexable insert: DC.. 0702..
 Minimum pre-drill $\varnothing D_{\min}$: 12 mm
 Minimum pre-drill $\varnothing D_{\min}$: 15 mm
 Centre offset L_3 : 7 mm

Technical description

ISO code toolholder	E10K SDUCR/L07
ISO code toolholder	E12M SDUCR/L07
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Centre offset L_3	7 mm
Centre offset L_3	9 mm
Clamping height L_2	9.6 mm
Clamping height L_2	11.6 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm

Minimum pre-drill $\varnothing D_{\min}$	15 mm
Overall length L	125 mm
Overall length L	150 mm
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws 10 pieces	269413
Set of insert screws Type 7	269028 7
Boring bar carbide Shank \varnothing / insert size 10/07 mm	260319 10/07
Boring bar carbide Shank \varnothing / insert size 12/07 mm	260319 12/07